

## TECHNICAL DATA

### Restorator<sup>®</sup> Odor-Neutralizing System

*The Superior **Alternative** to Ozone Generators*



Durable 22-gauge clad steel case & ABS end caps

Internal 40 CFM blower  
 11-watts (120V)

Galvanized steel grill

74-inch SVT power cord (120V)



Replaceable cartridge access

### SUGGESTED APPLICATIONS

- ◆ Fire/Flood Damage Restoration
- ◆ Vehicle Restoration/RV/Boat
- ◆ Contents Restoration
- ◆ Smoke Contaminated Hotel Rooms

- ◆ Real Estate/Foreclosures
- ◆ Crime Scene/Bioremediation
- ◆ Disaster Recovery
- ◆ Athletic Facilities

### IMPORTANT

This system provides a safe, effective *alternative* to ozone. It is *not* recommended for use with ozone generating equipment.

Use Xactimate codes: CLN DODRM, CLN DODRME, & CLN DODRMEM

Proudly made in the USA



Pioneering Simple Solutions for Tough Odors Naturally Since 1979



## The Restorator®

### Odor-Neutralizing System

#### PURPOSE

The Restorator is an easy-to-use, portable system. It treats areas up to 20,000 ft<sup>3</sup> to effectively eliminate odor contamination quickly and safely. Primarily intended for delivering a fast, high intensity treatment, it uses Vaportek's patented spill-proof essential oil cartridges to release a nontoxic, odor-neutralizing dry vapor into the air. Penetrating vapor quickly controls and eliminates malodor caused by smoke, humidity, food, and biological odors, among others. Based on proven technology originally developed for use in medical facilities, the Restorator sets the standard for treating an area's atmosphere, structure, and contents simultaneously.

#### PLACEMENT

The Restorator is intended for application where quick results are desired. Place on a firm, stable surface, situating the unit so air flow at both ends is unobstructed, preferably in a relatively high location. Deodorization may require as little as 15-60 minutes for light contamination. For more severe contamination, treatment may take several hours or days. If necessary, move the unit to different areas. As with any electrical device, do not locate or use near water. For best results, store cartridges in a cool, dry location and keep away from extreme heat. Dry vapor output will be affected by humidity, airflow, and temperature. Ideal dry vapor release occurs at 50-80°F. Vapor release significantly increases in excess of 90°F.

#### DETAILS

Easy portability and durable steel construction. No evacuation or recovery period is required with Vaportek technology. Not designed for continuous, long-term operation. Cartridge life is approximately 270 hours. The system does *not* create moisture or ozone, and will not harm fabric, plants, rubber, adhesives, electrical components, or remove pigment from leather. Vaportek products use natural essential oils. If an allergic reaction occurs, please discontinue use immediately. Approx. Dimensions: 7"H x 5"W x 11"L. Weight: 3 lbs., 12 oz. Five year limited warranty. CUL and CSA listed.



#### Works Fast

Odor neutralizer is immediate & permanent.



#### Safe & Environmentally Preferable

No chemicals or harmful ozone.



#### Easy-to-Use

Just uncap the cartridge, insert into machine, & turn on.

"We tried the Restorator & discovered that it did eliminate the odors—it didn't just mask them. All that remained was a nice, clean smell . . . Customers have complimented us on the cleanliness of our cars."

—Cobourg Taxi Company

" . . . The Restorator was run for exactly one hour & then removed. Every day for one week we opened the truck doors & checked for the cigarette smell. The odor was gone & it did not come back. That made believers out of us!"

—Lone Star Hubcap & Wheel

"After cleaning a customer's oriental wool carpet I could still detect a pet urine odor . . . I placed the exhaust end of the Restorator machine with a 3X Industrial cartridge directly over the urine odor location . . . The results truly amazed me!"

—Carpet Care of Chatham

#### Reorder Information:

Restorator (#90-5000)  
S.O.S./Smoke Odor Solution cartridge (#90-5150-85)  
3X Industrial cartridge (#90-5150)



# VAPORTEK®

P: 800.237.6367 | F: 262.246.5065

[www.vaportek.com](http://www.vaportek.com)

[www.facebook.com/vaportek](https://www.facebook.com/vaportek)

[www.linkedin.com/vaportek](https://www.linkedin.com/vaportek)

Sussex, WI USA

**NOTE:** Because we are committed to improving our products, Vaportek reserves the right to change product specifications and/or availability without notice or obligation.